

# Eaton 2100RNM-A2

Catalog Number: 2100RNM-A2

Eaton BR main lug loadcenter, Main lug only, 100 A, Aluminum, Non-metallic, NEMA 3R, 2 Circuits, 4 Spaces, Single-phase, 120/240 V, #14-2 AWG Cu/Al



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main lug loadcenter	2100RNM-A2
<b>UPC</b>	<b>Product Length/Depth</b>
786676208109	6.5 in
<b>Product Height</b>	<b>Product Width</b>
8.5 in	1.5 in
<b>Product Weight</b>	<b>Warranty</b>
1.5 lb	10 year
<b>Certifications</b>	
UL Listed	

## Product specifications

### Number of spaces

4

### Interrupt rating

10 kAIC

### Type

Main lug only

### Phase

Single-phase

### Wire size

#14-2 AWG Cu/Al

### Bus material

Aluminum

### Color

Non-metallic

### Enclosure

NEMA 3R

### Number of circuits

2

### Voltage rating

120/240 V

### Amperage Rating

100 A

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - 2100RNM-A2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)