

Eaton 2460SGNM

Catalog Number: 2460SGNM

Eaton BR main lug loadcenter,Includes GB4NM ground bar,60 A,2,Aluminum,NEMA 1,Surface,4 Circuits,2 Spaces,Three-wire,Single-phase,120/240 V,#14-2 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	2460SGNM
UPC	Product Length/Depth
786676369794	8.75 in
Product Height	Product Width
4.75 in	3.25 in
Product Weight	Warranty
0.95 lb	10 year
Certifications	
UL Listed	

Product specifications

Mounting

Surface

Number of spaces

2

Interrupt rating

10 kAIC

Type

Main lug loadcenter

Phase

Single-phase

Wire size

#14-2 AWG Cu/Al

Bus material

Aluminum

Number of wires

3

Enclosure

NEMA 1

Number of circuits

4

Voltage rating

120/240 V

Amperage Rating

60 A

Resources

Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - 2460SGNM](#)