

# Eaton 24INT125B

Catalog Number: 24INT125B

Eaton BR OEM interior assembly, BR style 1-inch loadcenter renewal part, interior assembly, 125A, single-phase, 4 circuits, 2 spaces, (1) 1/0-#14 AWG Cu, 2/0-12 AWG Al at 60°C or 75°C, aluminum bus

## General specifications



### Product Name

Eaton BR OEM interior assembly

### Catalog Number

24INT125B

### UPC

786676001885

### Product Length/Depth

10 in

### Product Height

1 in

### Product Width

8 in

### Product Weight

0.5 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

Federal Specifications Classification W-P-115B, Type 1 and Class 2 Requirements

### Certifications

Contact Manufacturer

## Product specifications

### Number of spaces

2

### Type

Interior assembly

### Cover

Cover not included

### Phase

Single-phase

### Wire size

#14-1/0 AWG Cu or #12-2/0 AWG Al

### Bus material

Aluminum

### Number of wires

3

### Number of circuits

4

### Voltage rating

120/240 V

### Amperage Rating

125A

### Number Of Poles

Four-pole

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - 24INT125B](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)