

Eaton 454D507G02

Catalog Number: 454D507G02

Eaton Navy and Marine complete molded case circuit breaker, ALB-1, Fixed thermal, fixed magnetic trip, Single-pole, 10A, 125 V/dc, 5 kAIC at 125 V, 2.5 kAIC at 125 Vdc, Line and load, Naval, 60/400 Hz, Clamp type stab, Pressure

General specifications



Product Name	Catalog Number
Eaton Navy & Marine complete molded case circuit breaker	454D507G02
	UPC
	786679836521
Product Length/Depth	Product Height
4.1 in	1.1 in
Product Width	Product Weight
3.3 in	0.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year MIL-DTL-17361 from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NSN 5925-00-204-7488

Product specifications

Line

Clamp type stab

Prod load

Pressure

Interrupt rating

5 kAIC at 125 Vac

2.5 kAIC at 125 Vdc

Circuit breaker type

ALB-1

Frequency rating

60 to 400 Hz

Class

Naval

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Voltage rating

125 Vac/dc

Amperage Rating

10 A

Trip Type

Fixed thermal, fixed magnetic

Number of poles

Single-pole

Resources

Catalogs

[Circuit Breakers Naval Shipboard Use](#)

[Molded case circuit breakers catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - 454D507G02](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)