

Eaton 83E8866

Catalog Number: 83E8866

Eaton Series C complete molded case circuit breaker, R-frame, RD, Three-pole, 2000A, 600 Vac, 50 kAIC, Line and load, Auxiliary Switch, Undervoltage release, ON-OFF hasp factory lock



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	83E8866
	UPC 782116144587
Product Length/Depth	Product Height
1.1 in	1.1 in
Product Width	Product Weight
1.1 in	1.1 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Product specifications

Interrupt rating

50 kAIC

Circuit breaker type

RD

Undervoltage release

Undervoltage release

Terminals

Line and load

Voltage rating

600 Vac

Amperage Rating

2000 A

Auxiliary switch

Auxiliary Switch

Lockout type

ON-OFF hasp factory lock

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Multi-wire lugs product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - 83E8866](#)