

Eaton BD3015BP100

Catalog Number: BD3015BP100

Eaton BR thermal magnetic circuit breaker, Type BD 1-Inch CTL plug-on circuit breaker, Includes rejection tab feature, bulk pack, 30-15 A, 10 kAIC, Single-pole, 120V, BD, #14-4 AWG Cu/Al, BD, Type BR Loadcenters



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BD3015BP100
	UPC
	782116324828
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
1 in	0.3 lb
Warranty	Compliances
Limited lifetime residential, 1 year commercial	Federal Specifications Classification W-C375
Certifications	Catalog Notes
UL 489	All Type BD Duplex and BQ Quadplex circuit breakers carry listing for HACR applications. All 15 and 20 ampere single poles are switch duty rated.

Product specifications

Special features

Includes rejection tab feature, bulk pack

Interrupt rating

10 kAIC

Type

Type BD 1-Inch CTL plug-on circuit breaker

Wire size

#14-4 AWG Cu/Al

Circuit breaker type

BR

Used with

Type BR Loadcenters

Main circuit breaker

BD

Mounting Method

Plug-on

Voltage rating

120 V

Amperage Rating

(1) 30A, (1) 15A

Number of poles

Single-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BD3015BP100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)