

Eaton BR1224L125

Catalog Number: BR1224L125

Eaton Eaton BR main lug loadcenter ,No feed-thru lugs,Main lug,200 A,D1R,Aluminum,Cover included,NEMA 3R,Metallic,25 kAIC,BWH,NEMA 3R,40 Circuits,Twenty-four pole,30 Spaces,Three-wire

General specifications



Product Name

Eaton BR main lug loadcenter

UPC

786676446556

Product Height

16.75 in

Product Weight

15.6 lb

Certifications

UL 67

UL 50

Catalog Number

BR1224L125

Product Length/Depth

3.88 in

Product Width

14.31 in

Warranty

10 year

Catalog Notes

Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard. Has notch for brhdk125 hold-down kit.

Product specifications

Number of spaces

12

Special features

No feed-thru lugs, includes BREQS125 hold-down screw

Interrupt rating

10 kAIC

Phase

Single-phase

Wire size

#6-2/0 AWG Cu/Al

Bus material

Aluminum

Main circuit breaker

BR

Enclosure

NEMA 1

Amperage Rating

125 A

Mounting

Combination

Enclosure material

Metallic

Type

Main lug

Cover

Cover included

Used with

Type BR 1-inch breakers

Number of wires

3

Number of circuits

24

Voltage rating

120/240V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type BR Arc Fault Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Specifications and datasheets

[Eaton Specification Sheet - BR1224L125](#)

Box size

B1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia