

# Eaton BRP30B100V25

Catalog Number: BRP30B100V25

Value pack, Plug-on neutral main circuit breaker loadcenter, 100A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, BR, 60 circuits, 30 spaces, Three-wire, Single-phase, #4-1/0 AWG Cu/Al, Combination, Type BR 1-inch breakers, 120/240V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP30B100V25
<b>UPC</b>	<b>Product Length/Depth</b>
786689058234	29.12 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
27 lb	10 year
<b>Certifications</b>	
UL 67	
UL 50	

## Product specifications

### Number of spaces

30

### Special features

Value pack

### Interrupt rating

10 kAIC

### Phase

Single-phase

### Wire size

#4-1/0 AWG Cu/Al

### Bus material

Aluminum

### Main circuit breaker

BR

### Enclosure

NEMA 1

### Amperage Rating

100 A

### Number Of Poles

Single-pole

### Mounting

Combination

### Enclosure material

Metallic

### Type

Plug-on neutral main circuit breaker loadcenter

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### Number of wires

3

### Number of circuits

60

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30B100V25](#)

Voltage rating

120/240 V

Box size

X5



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)