

# Eaton BRP30B200

Catalog Number: BRP30B200

Eaton BR main breaker loadcenter, Ground bar, includes BREQS125 hold-down screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR2200, 60 circuits, Single pole, 30 spaces



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP30B200
<b>UPC</b>	<b>Product Length/Depth</b>
786689044060	34.12 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
31.1 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## Product specifications

### Number of spaces

30

### Special features

Ground bar, includes BREQS125 hold-down screw

### Interrupt rating

25 kAIC

### Phase

Single-phase

### Bus material

Aluminum

### Main circuit breaker

CSR2200

### Enclosure

NEMA 1

### Amperage Rating

200 A

### Number Of Poles

Single-pole

### Mounting

Combination

### Enclosure material

Metallic

### Type

Plug-on neutral main circuit breaker loadcenter

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### Number of wires

Two hots, neutral and ground

### Number of circuits

60

### Voltage rating

120/240 V

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP30B200](#)

Box size

X6



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)