

Eaton BRP40B200

Catalog Number: BRP40B200

Eaton BR main breaker loadcenter, Ground bar, includes BREQS125 hold-down screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X8, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR, 80 circuits, Single pole, 40 spaces

General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40B200
UPC	Product Length/Depth
786689044053	39 in
Product Height	Product Width
3.88 in	15.5 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 67	
UL 50	



Product specifications

Number of spaces

40

Special features

Ground bar, includes BREQS125 hold-down screw

Interrupt rating

25 kAIC

Phase

Single-phase

Bus material

Aluminum

Main circuit breaker

CSR

Enclosure

NEMA 1

Amperage Rating

200 A

Number Of Poles

Single-pole

Mounting

Combination

Enclosure material

Metallic

Type

Plug-on neutral main circuit breaker loadcenter

Cover

Cover included

Used with

Type BR 1-inch breakers

NEMA rating

NEMA 1

Number of circuits

80

Voltage rating

120/240 V

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP40B200](#)

Box size

X8



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)