

Eaton CH170ST

Catalog Number: CH170ST

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 70 A, 10 kAIC, Single-pole, 120/240V, CH, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters, Shunt trip included

General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CH170ST
	UPC
	782113878119
Product Length/Depth	Product Height
4.8 in	3.5 in
Product Width	Product Weight
3.5 in	0.55 lb
Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489
	Catalog Notes
	Single-Pole 120/240V Requires one 3/4-Inch space.



Product specifications

Special features

Shunt Trip

Interrupt rating

10 kAIC

Type

Type CH 3/4-Inch standard circuit breaker

Wire size

#10-1/0 AWG Cu/Al

Circuit breaker type

CH

Used with

Type CH Loadcenters

Shunt trip

Included

Main circuit breaker

CH

Voltage rating

120/240 V

Amperage Rating

70A

Number of poles

Single-pole

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CH170ST



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia