

Eaton CH214MTBLB

Catalog Number: CH214MTBLB

Eaton meter socket, Safety socket, 125A, Over/under, 4-jaw, 1-ph, Depends on selected main circuit breaker, 3-wire, Provisions, order plug in type Type BR, BRN, BRHH breakers separately, Type BR, BRN, BRHH breakers, 240 Vac

General specifications

Product Name

Eaton meter socket

Catalog Number

CH214MTBLB

UPC

782116164929

Product Length/Depth

42 in

Product Height

6 in

Product Width

7 in

Product Weight

28 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed



Product specifications

Secondary circuit breaker

Provisions

Interrupt rating

Depends on selected main circuit breaker

Type

Safety socket

Feed type

Top/bottom

Phase

Single-phase

Wire size

#14-2/0 AWG

Number of jaws

Four-jaw

Number of wires

Three-wire

Voltage rating

240V

Amperage Rating

125A

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH214MTBLB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)