

# Eaton CH350SWST

Catalog Number: CH350SWST

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch neutral switching circuit breaker, 50 A, 10 kAIC, Three-pole, 120/240V, CH, Common breaker trip, #14-8 AWG Cu/Al, CH, Type CH Loadcenters, Switching neutral, Shunt trip included



## General specifications

### Product Name

Eaton CH thermal magnetic circuit breaker

### Catalog Number

CH350SWST

### UPC

782114100714

### Product Length/Depth

3 in

### Product Height

2.8 in

### Product Width

2.3 in

### Product Weight

0.9 lb

### Warranty

Limited lifetime residential, 1 year commercial

### Certifications

UL 489

### Catalog Notes

Three-Pole 120/240V Common Trip  
Requires Three 3/4 in Spaces, For circuit breakers with Shunt Trip, add ST suffix.  
Shunt trip requires one additional pole.

## Product specifications

### Neutral

Switching neutral

### Interrupt rating

10 kAIC

### Type

Type CH 3/4-Inch neutral switching circuit breaker

### Wire size

#14-8 AWG Cu/Al

### Circuit breaker type

CH

### Used with

Type CH Loadcenters

### Shunt trip

Included

### Main circuit breaker

CH

### Voltage rating

120/240 V

### Amperage Rating

50 A

### Trip Type

Common breaker trip

### Number of poles

Three-pole

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Specifications and datasheets

Eaton Specification Sheet - CH350SWST



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)