

# Eaton CH9526K7

Catalog Number: CH9526K7

Eaton K-Base Socket, Three-phase, four-wire, Overhead/underground feed, Steel enclosure, Seven-jaws, 480A

## General specifications

Product Name	Catalog Number
Eaton K-Base socket	CH9526K7
UPC	Product Length/Depth
782116122080	20.42 in
Product Height	Product Width
43.08 in	6.39 in
Product Weight	Warranty
75 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	



## Product specifications

### Enclosure material

Steel

### Feed type

Top/bottom

### Phase

Three-phase

### Number of jaws

Seven-jaw

### Amperage Rating

480A

### Hub type

(2) 5 x 5 hub opening

## Resources

### Brochures

[Single Meter Sockets](#)

### Drawings

[Dimensional Drawing - K7T RINGLESS METER SOCKET, STEEL, 2 LARGE HUB OPENINGS](#)

### Specifications and datasheets

[Metering Equipment - Florida Meter Group \(FMG\)](#)

[Eaton Specification Sheet - CH9526K7](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)