

Eaton CHM1N1NSXU

Catalog Number: CHM1N1NSXU

Eaton pedestal mount metered, Metered-ring, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 6, NEMA 14-50R, NEMA 14-50R



General specifications

Product Name

Eaton pedestal mount metered

Catalog Number

CHM1N1NSXU

UPC

786685403250

Product Length/Depth

7.25 in

Product Height

31 in

Product Width

10 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Feed type

Bottom

Mounting

Surface

Number of circuits

6

Receptacle center

NEMA 14-50R

Receptacle left

NEMA 14-50R

Receptacle right

None

Type

Metered-ring

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHM1N1NSXU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)