

Eaton CHRDG9N9NS

Catalog Number: CHRDG9N9NS

Eaton pedestal mount metered, Top, Surface, Circuits: 4, Weather-resist and tamper resist center and right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA L14-30R, Right: NEMA 5-20R2GFI WR TR, Ringless



General specifications

Product Name

Eaton pedestal mount metered

Catalog Number

CHRDG9N9NS

UPC

786685703428

Product Length/Depth

7.4 in

Product Height

30.9 in

Product Width

9.8 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle

Weather-resistant/tamper resistant center/right receptacle

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA L14-30R

Receptacle right

NEMA 5-20R2GFI

Type

Metered-ringless

Miscellaneous

Utility approvals

IA : Alliant (IP&L and WP&L)

FL : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

IN : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

KY : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

NC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

OH : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

SC : MEG (Duke Energy, Florida Power, Tampa Electric, Gulf Power, Oklahoma Gas and Electric)

FL : Tallahassee City Electric

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHRDG9N9NS](#)