

# Eaton CHU1N4N4NS

Catalog Number: CHU1N4N4NS

Eaton pedestal mount unmetered, Unmetered, 50A, 30A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 14-50R, NEMA TT-30R, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V

## General specifications



### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU1N4N4NS

### UPC

786685182223

### Product Length/Depth

4.3 in

### Product Height

17.1 in

### Product Width

9.5 in

### Product Weight

0.01 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA TT-30R

### Receptacle left

NEMA 14-50R

### Receptacle right

NEMA TT-30R

### Type

Unmetered

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHU1N4N4NS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)