

# Eaton CHU1N4NP

Catalog Number: CHU1N4NP

Eaton pedestal mount unmetered, Unmetered, 50A, 30A, None, Non-ground fault, Non-ground fault, None, Top, Pedestal, Circuits: 4, NEMA 14-50R, NEMA TT-30R, None, 4, 3, 0, 125/250V, 125V, None

## General specifications



### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU1N4NP

### UPC

782114203156

### Product Length/Depth

6.8 in

### Product Height

39.9 in

### Product Width

9.5 in

### Product Weight

30 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL 231

UL Listed file E163588

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Feed type

Top

### Mounting

Pedestal

### Number of circuits

4

### Receptacle center

NEMA TT-30R

### Receptacle left

NEMA 14-50R

### Receptacle right

None

### Type

Unmetered

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - POWER OUTLET, UNMETERED PEDESTAL EXTENSION

### Specifications and datasheets

Eaton Specification Sheet - CHU1N4NP



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia