

Eaton CHU1N9N4NP

Catalog Number: CHU1N9N4NP

Eaton pedestal mount unmetered, Water and tamper resistant center receptacle, Unmetered, 50A, 20A, 30A, Non-GF, Non-GF, Non-ground fault, Top, Pedestal, Circuits: 4, NEMA 14-50R, NEMA 5-20R2GF, NEMA TT-30R, 4, 3, 3, 125/250V, 125V, 125V



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU1N9N4NP
UPC	Product Length/Depth
786685443294	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
35 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Pedestal

Number of circuits

4

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 14-50R

Receptacle right

NEMA TT-30R

Type

Unmetered

Miscellaneous

Special features

Water and tamper resistant center receptacle

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHU1N9N4NP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia