

Eaton CHU1N9N4NPL

Catalog Number: CHU1N9N4NPL

Eaton Temporary Power/RV Park Pedestal, Unmetered POP, Four-circuit, Pedestal mount, Top feed, Receptacle type Left: NEMA 14-50R Non-GF, Center: NEMA 5-20R2GFI tamper/weather resistant Non-GF, Right: NEMA TT-30R Non-GF, Lighted



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU1N9N4NPL
UPC	Product Length/Depth
786689055578	9.75 in
Product Height	Product Width
40.625 in	7.375 in
Product Weight	Warranty
35 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed file E163588 UL 231	For receptacle configurations, see table in catalog.

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Pedestal

Number of circuits

4

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA TT-30R

Type

Unmetered

Miscellaneous

Special features

Lighted

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU1N9N4NPL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia