

# Eaton CHU224MTBLB

Catalog Number: CHU224MTBLB

Eaton pedestal mount unmeteread, Unmetered, 200A, Underground, Provisions, Back-to-back pedestal, Four-jaw, Three-wire, Single-phase, Ring, Type CH breakers, 120/240V, #6 AWG-250 kcmil

## General specifications

### Product Name

Eaton pedestal mount unmeteread

### Catalog Number

CHU224MTBLB

### UPC

782116164981

### Product Length/Depth

13.6 in

### Product Height

39.9 in

### Product Width

9.5 in

### Product Weight

40 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Order Type CC breaker or CCH breaker separately.



## Physical Attributes

### Feed type

Bottom

### Main circuit breaker

Provisions

### Number of jaws

Four-jaw

### Number of wires

Three-wire

### Type

Pedestal mount unmetrated

## Performance Ratings

### Interrupt rating

10 kAIC

### Phase

Single-phase

### Voltage rating

120/240 V

## Miscellaneous

### Used with

Type CH breakers

### Utility approvals

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

WA : Puget Sound Energy

WA : Tacoma Public Utilities

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Specifications and datasheets

Eaton Specification Sheet - CHU224MTBLB



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia