

# Eaton CHU224MTBP

Catalog Number: CHU224MTBP

Eaton pedestal mount unmetered, Unmetered, With T-Fuse switch, 200A, Underground, Pedestal, Four-jaw, Three-wire, Single-phase, 200A, Ring, 120/240V, #6 AWG-250 kcmil

## General specifications

### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU224MTBP

### UPC

782116153756

### Product Length/Depth

6.8 in

### Product Height

39.9 in

### Product Width

9.5 in

### Product Weight

30 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed



## Physical Attributes

### Feed type

Bottom

### Number of jaws

Four-jaw

### Number of wires

Three-wire

### Type

Pedestal mount unmetered

## Performance Ratings

### Interrupt rating

10 kAIC

### Phase

Single-phase

### Voltage rating

120/240 V

## Miscellaneous

### Utility approvals

CA : Pacific Gas and Electric (PG&E)

CA : Sacramento Municipal Utility District (SMUD)

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHU224MTBP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)