

# Eaton CHU227MTBHMS15

Catalog Number: CHU227MTBHMS15

Eaton pedestal mount unmeteread, Unmetered, 200A, Underground, 25 kAIC, JD3200, Surface, Seven-jaw, Four-wire, Three-phase, Ring, Type CH breakers, 480/277V, #6 AWG-250 kcmil

## General specifications

### Product Name

Eaton pedestal mount unmeteread

### Catalog Number

CHU227MTBHMS15

### UPC

782116165032

### Product Length/Depth

13.6 in

### Product Height

39.9 in

### Product Width

9.5 in

### Product Weight

51 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed



## Physical Attributes

### Feed type

Bottom

### Main circuit breaker

JD3200

### Number of jaws

Seven-jaw

### Number of wires

Four-wire

### Security

Ring

### Type

Pedestal mount unmetered

## Performance Ratings

### Amperage Rating

200 A

### Interrupt rating

10 kAIC

### Phase

Three-phase

### Voltage rating

480/277 V

## Miscellaneous

### Used with

Type CH breakers

### Utility approvals

ID : Idaho Power

OR : Idaho Power

WA : Seattle City Light

AK : Anchorage Municipal Light & Power

NV : NV Energy

CA : City of Los Angeles - DWP (LADWP)

AZ : Southern California Edison

CA : Southern California Edison

WA : Puget Sound Energy

WA : Tacoma Public Utilities

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Specifications and datasheets

Eaton Specification Sheet - CHU227MTBHMS15



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)