

Eaton CHU4N4N4NS

Catalog Number: CHU4N4N4NS

Eaton pedestal mount unmetered, Unmetered, 30A, 30A, 30A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA TT-30R, NEMA TT-30R, 3, 3, 3, 125V, 125V, 125V



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU4N4N4NS
UPC	Product Length/Depth
786685984360	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
14.9 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA TT-30R

Receptacle left

NEMA TT-30R

Receptacle right

NEMA TT-30R

Type

Unmetered

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHU4N4N4NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia