

Eaton CHU4N4NB

Catalog Number: CHU4N4NB

Eaton pedestal mount unmetered, Unmetered, 30A, 30A, None, Non-ground fault, Non-ground fault, None, Top, Back-to-back pedestal, Circuits: 4, NEMA TT-30R, NEMA TT-30R, None, 3, 3, 0, 125V, 125V, None



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU4N4NB
UPC	Product Length/Depth
782116094714	4.3 in
Product Height	Product Width
17.1 in	9.5 in
Product Weight	Warranty
50 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588
UL 231

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Feed type

Top

Mounting

Back-to-back pedestal

Number of circuits

4

Receptacle center

NEMA TT-30R

Receptacle left

NEMA TT-30R

Receptacle right

None

Type

Unmetered

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - POWER OUTLET, UNMETERED BACK TO BACK](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU4N4NB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)