

# Eaton CHU4N9NS

Catalog Number: CHU4N9NS

Eaton pedestal mount unmetered, Water and tamper resistant center receptacle, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI (3), None, 3, 3, 0, 125V, 125V, None

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount unmetered	CHU4N9NS
<b>UPC</b>	<b>Product Length/Depth</b>
786685406350	18.25 in
<b>Product Height</b>	<b>Product Width</b>
8 in	10.25 in
<b>Product Weight</b>	<b>Warranty</b>
15.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.



## Certifications

UL Listed file E163588  
UL 231

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

None

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2GF

### Receptacle left

NEMA TT-30R

### Receptacle right

None

### Type

Unmetered

## Miscellaneous

### Special features

Water and tamper resistant center receptacle

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHU4N9NS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)