

# Eaton CHU9N9N9N9NB

Catalog Number: CHU9N9N9N9NB

Eaton pedestal, Back to back mount, Unmetered, 4 circuit, Top feed, Receptacles: (4) NEMA 5-20R2GFI20A Weather-resistant/tamper resistant non-GF

## General specifications



### Product Name

Eaton pedestal mount unmetered

### Catalog Number

CHU9N9N9N9NB

### UPC

786689060411

### Product Length/Depth

14.25 in

### Product Height

40.625 in

### Product Width

9.75 in

### Product Weight

50 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588  
UL 231

### Catalog Notes

See catalog notes for receptacle configurations

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Feed type

Top

### Mounting

Back to back

### Number of circuits

4

### Receptacle

Weather-resistant/tamper resistant left/center/right receptacle

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

NEMA 5-20R2GFI

### Type

Unmetered

## Resources

### Specifications and datasheets

Eaton Specification Sheet - CHU9N9N9N9NB



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia