

# Eaton CHU9NPXL

Catalog Number: CHU9NPXL

Eaton pedestal mount unmetered, Lighted, Water and tamper resistant left receptacle, Unmetered, 20A, None, None, Non-ground fault, None, None, Top, Pedestal, Circuits: 6, NEMA 5-20R2GFI(3), None, None, 3, 0, 0, 125V, None, None

## General specifications

|                                |  |
|--------------------------------|--|
| <b>Product Name</b>            | <b>Catalog Number</b>  |
| Eaton pedestal mount unmetered | CHU9NPXL   |
| <b>UPC</b>                     | <b>Product Length/Depth</b>  |
| 786685985305                   | 4.3 in   |
| <b>Product Height</b>          | <b>Product Width</b>   |
| 17.1 in                        | 9.5 in   |
| <b>Product Weight</b>          | <b>Warranty</b>  |
| 34.9 lb                        | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>Certifications</b>          |  |
| UL 231                         |  |
| UL Listed file E163588         |  |



## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 3

None

### Feed type

Top

### Illumination

Lighted

### Mounting

Pedestal

### Number of circuits

6

### Receptacle left

NEMA 5-20R2GFI WRTR

### Receptacle right

None

### Type

Unmetered

## Miscellaneous

### Special features

Water and tamper resistant left receptacle

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHU9NPXL](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)