

Eaton CHUANS

Catalog Number: CHUANS

Eaton pedestal mount unmetered, Unmetered, 50A, None, None, Non-ground fault, None, None, Top, Surface, Circuits: 4, NEMA L14-50R, None, None, 3, 0, 0, 125/250V, None, None

General specifications

Product Name

Eaton pedestal mount unmetered

Catalog Number

CHUANS

UPC

786689014933

Product Length/Depth

4.3 in

Product Height

17.1 in

Product Width

9.5 in

Product Weight

15 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588



Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

None

Circuit breaker position 3

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

None

Receptacle left

NEMA L14-50R

Receptacle right

None

Type

Unmetered

Resources

Application notes

Eaton Specification Sheet - CHUANS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)