

Eaton CHUHGJGB

Catalog Number: CHUHGJGB

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, None, Ground fault, Ground fault, None, Top, Back-to-back pedestal, Circuits: 4, NEMA L6-20R, NEMA L5-20R, None, 3, 3, 0, 250V, 125V, None

General specifications

Product Name

Eaton pedestal mount unmetered

Catalog Number

CHUHGJGB

UPC

786685236735

Product Length/Depth

13.6 in

Product Height

39.9 in

Product Width

9.5 in

Product Weight

50 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231

UL Listed file E163588



Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Ground fault

Circuit breaker position 3

None

Feed type

Top

Mounting

Back-to-back pedestal

Number of circuits

4

Receptacle center

NEMA L5-20R

Receptacle left

NEMA L6-20R

Receptacle right

None

Type

Unmetered

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHUHGJGB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)