

Eaton CHUHN4N1NPX

Catalog Number: CHUHN4N1NPX

Eaton pedestal mount unmetered, Unmetered, 20A, 30A, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Top, Pedestal, Circuits: 6, NEMA L6-20R, NEMA TT-30R, NEMA 14-50R, 3, 3, 4, 250V, 125V, 250V



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHUHN4N1NPX
UPC	Product Length/Depth
786685858067	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
35 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Top

Mounting

Pedestal

Number of circuits

6

Receptacle center

NEMA TT-30R

Receptacle left

NEMA L6-20R

Receptacle right

NEMA 14-50R

Type

Unmetered

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHUHN4N1NPX](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)