

Eaton CHWPS2040DL

Catalog Number: CHWPS2040DL

Eaton pressure switch, Low pressure cut-off, Water pressure switch, NEMA 1, CH breaker, Single-phase, 20-40 PSI, 120/240V

General specifications



Product Name
Eaton pressure switch

Catalog Number
CHWPS2040DL

UPC
782116183869

Product Length/Depth
3.74 in

Product Height
3.93 in

Product Width
3.54 in

Product Weight
0.99 lb

Warranty
3 year

Certifications
UL Listed
CSA Certified

Catalog Notes
Main tenant breakers can exit top, bottom or back. If being used in outdoor application and exiting the top, mount Myer type hubs on rainproof cap.
208Y/120V, three-phase, four-wire
240/120V, three-phase, four-wire delta
B-phase is high leg

Product specifications

Special features

Low pressure cut-off

Type

Water pressure switch

Phase

Single-phase

Main circuit breaker

CH

Enclosure

NEMA 1

Voltage rating

120/240 V

Pressure rating

20-40 PSI

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHWPS2040DL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)