

# Eaton CN35GNY2AB

Catalog Number: CN35GNY2AB

Eaton CN35 electrically held lighting contactor, 60 A, 1 NO, 60 A, 25 hp, Three-pole, Electrically held, 2, CN35 Series, Lighting contactors

## General specifications



|   |                       |
|---|-----------------------|
| <b>Product Name</b>                             | <b>Catalog Number</b> |
| Eaton CN35 electrically held lighting contactor | CN35GNY2AB            |
|   | UPC                   |
|   | 786685385396          |
| <b>Product Length/Depth</b>                     | <b>Product Height</b> |
| 4.44 in   | 5.05 in               |
| <b>Product Width</b>                            | <b>Product Weight</b> |
| 2.56 in   | 3.5 lb                |
| <b>Warranty</b>                                 | <b>Certifications</b> |
| 1 year  | UL Listed             |

## Product specifications

### Number Of Poles

Three-pole

## Resources

### Brochures

[Lighting contactors](#)

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

### Specifications and datasheets

[Quick Selector - Lighting Contactors](#)

[Eaton Specification Sheet - CN35GNY2AB](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)