

Eaton D20425

Catalog Number: D20425

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 230 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 230Y/133V, 150°C, 20 kVA, Al windings, Frame: 912B, uses WS38

General specifications

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton Drive isolation ventilated transformer | D20425 |
| | UPC |
| | 786680330032 |
| Product Length/Depth | Product Height |
| 16.5 in | 30 in |
| Product Width | Product Weight |
| 23 in | 254 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |



Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

912B

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Horsepower

15 hp

Phase

Three-phase

Primary voltage

230 V

Secondary Voltage

230Y/133 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - D20425](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)