

Eaton D35405

Catalog Number: D35405

Drive Isolation Transformer, Ventilated, Dry Type Distribution, DT-3, Three-phase, PV: 460 delta, Taps: 1 at +5% FCAN, 1 at -5% FCBN, SV: 230Y/133V, 150°C, 145 kVA, Al windings, Frame: 916A, uses WS19

General specifications

Product Name	Catalog Number
Eaton Drive isolation ventilated transformer	D35405
	UPC
	786680331459
Product Length/Depth	Product Height
23.42 in	48.56 in
Product Width	Product Weight
28.22 in	918 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Frame

916A

Tap size

1 at +5% FCAN, 1 at -5% FCBN

Type

Dry Type Distribution, Drive Isolation Transformer

Performance Ratings

Frequency rating

60 Hz

Horsepower

125 hp

Kva Rating

145 kVA

Phase

Three-phase

Primary voltage

460 V

Secondary Voltage

230Y/133 V

Temperature rise

150 °C rise

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - D35405](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)