

Eaton E50AR1SY1

Catalog Number: E50AR1SY1

Eaton E50 NEMA heavy duty plug-in limit switch,Cable with 4 Pin Deutsch Connector,10A at 240Vac,1A at 250Vdc,SOOW-A,1NO-1NC,96Foot,Die Cast Zinc,NEMA 1,3,3S,4,4X,6,6P,13,IP67,10A,1A,10°to201°F(-12°to94°C),Side Rotary

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50AR1SY1
	UPC 786685232195
Product Length/Depth	Product Height
1.54 in	4.22 in
Product Width	Product Weight
2.46 in	2.1 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Contact configuration

1 NO-1 NC

Switch type

Side rotary

Cord length

96 ft

Operating temperature - min

10 °F

Maximum AC current

10 A

Maximum DC current

1 A

Connection

Cable with 4-pin Deutsch connector

Cable type

SOOW-A

Enclosure material

Die cast zinc

Accuracy

Refer to installation publication P15836

Contact Rating

10A at 240Vac, 1A at 250Vdc

Operating temperature - max

201 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Resources

Catalogs

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E50AR1SY1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)