

Eaton E50ARY4

Catalog Number: E50ARY4

Eaton E50 NEMA heavy duty plug-in limit switch, Refer to installation publication P15836, 8 Ft. (2.5m) Cable, 10A at 240Vac, 1A at 250Vdc, 1NO, Die Cast Zinc, 10A, 1A, 10° to 201°F (-12° to 94°C), Side Rotary



General specifications

| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton E50 NEMA heavy duty plug-in limit switch | E50ARY4 |
| | UPC |
| | 782113650524 |
| Product Length/Depth | Product Height |
| 1.54 in | 5.23 in |
| Product Width | Product Weight |
| 2.41 in | 1.37 lb |
| Warranty | Compliances |
| 1 year | RoHS Compliant |
| Certifications | |
| UL Listed | |
| CSA Certified | |

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO

Accuracy

Refer to installation publication P15836

Switch type

Side rotary

Contact Rating

10A at 240Vac, 1A at 250Vdc

Operating temperature - min

10 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

201 °F

Connection

8 ft (2.4 m) cable

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50ARY4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)