

Eaton E50ARY5

Catalog Number: E50ARY5

Eaton E50 NEMA heavy duty plug-in limit switch, Refer to installation publication P15836, 8 Ft. (2.5m) Cable, 10A at 240Vac, 1A at 250Vdc, 1NC, Die Cast Zinc, 10A, 1A, 10° to 201°F (-12° to 94°C), Side Rotary



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50ARY5
	UPC
	782113650371
Product Length/Depth	Product Height
1.54 in	5.23 in
Product Width	Product Weight
2.41 in	1.37 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NC

Accuracy

Refer to installation publication P15836

Switch type

Side rotary

Contact Rating

10A at 240Vac, 1A at 250Vdc

Operating temperature - min

10 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

201 °F

Connection

8 ft (2.4 m) cable

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50ARY5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)