

Eaton E50AS3P4

Catalog Number: E50AS3P4

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, Within 0.003,4 Pin M12 Connector, 10A at 240Vac, 1A at 250Vdc, 1NO-1NC, Die Cast Zinc, NEMA 1,3,3S,4,4X,6,6P,13,IP67,IP69K,10A,1A,14° to 201°F (-10° to 94°C), Side Push Roller



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50AS3P4 switch	UPC 782114627969
Product Length/Depth	Product Height
1.54 in	4.67 in
Product Width	Product Weight
2.94 in	1.275 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Accuracy

Within 0.003

Switch type

Side push roller

Contact Rating

10A at 240Vac, 1A at 250Vdc

Operating temperature - min

14 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

201 °F

Connection

4-pin M12 connector

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50AS3P4](#)