

Eaton E50AW16PY1

Catalog Number: E50AW16PY1

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch,8 Ft. (2.5m) Cable,10A at 240Vac,1A at 250Vdc,SOOW-A,1NO-1NC,96Foot,Die Cast Zinc,NEMA 1,3,3S,4,4X,6,6P,13,IP67,IP69K,10A,1A,14° to 221°F (-10° to 105°C),Wobble Stick



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50AW16PY1 switch	UPC 786685354507
Product Length/Depth	Product Height
1.54 in	5.38 in
Product Width	Product Weight
1.58 in	2.1 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Switch type

Wobble stick

Contact Rating

10A at 240Vac, 1A at 250Vdc

Cord length

96 ft

Operating temperature - min

14 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

221 °F

Connection

8 ft (2.4 m) cable

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Cable type

SOOW-A

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50AW16PY1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)