

Eaton E50DN2Y4

Catalog Number: E50DN2Y4

Eaton E50 NEMA heavy duty plug-in limit switch, Refer to installation publication P15836, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 250°F (-10° to 121°C), Neutral Position



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50DN2Y4
	UPC
	786685117072
Product Length/Depth	Product Height
1.54 in	1.05 in
Product Width	Product Weight
2.46 in	0.4 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Accuracy

Refer to installation publication P15836

Switch type

Neutral position

Operating temperature - min

14 °F

Operating temperature - max

250 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50DN2Y4](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)