

# Eaton E50DS3Y2

Catalog Number: E50DS3Y2

Eaton E50 NEMA heavy duty plug-in limit switch, Within 0.003, Die Cast Zinc, -40° to 201°F (-40° to 94°C), Side Push Roller



## General specifications

**Product Name**  
Eaton E50 NEMA heavy duty plug-in limit switch

**Catalog Number**

UPC

782113915388

**Product Length/Depth**

1.54 in

**Product Height**

1.05 in

**Product Width**

2.94 in

**Product Weight**

0.4 lb

**Warranty**

1 year

**Compliances**

RoHS Compliant

**Certifications**

UL Listed

CSA Certified

## Product specifications

### Enclosure material

Die cast zinc

### Accuracy

Within 0.003

### Switch type

Side push roller

### Operating temperature - min

-40 °F

### Operating temperature - max

201 °F

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - E50DS3Y2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)