

Eaton E50RY5

Catalog Number: E50RY5

Eaton E50 NEMA heavy duty plug-in limit switch, Refer to installation publication P15836, 8 Ft. (2.5m) Cable, Die Cast Zinc, 10° to 201°F (-12° to 94°C)



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50RY5
	UPC
	782113577739
Product Length/Depth	Product Height
1.54 in	3.53 in
Product Width	Product Weight
1.06 in	0.5688 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Accuracy

Refer to installation publication P15836

Operating temperature - min

10 °F

Operating temperature - max

201 °F

Connection

8 ft (2.4 m) cable

Resources

Specifications and datasheets

[Eaton Specification Sheet - E50RY5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)