

Eaton E50SA6PT

Catalog Number: E50SA6PT

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, 5 Pin Mini Pigtail Connector, 10A at 240Vac, 1A at 250Vdc, SOOW-A, 1NO-1NC, 36ft, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K, 10A, 1A, -29° to 221°F (-34° to 105°C)



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50SA6PT
	UPC 782113726410
Product Length/Depth	Product Height
1.54 in	3.58 in
Product Width	Product Weight
1.58 in	2.1188 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Contact Rating

10A at 240Vac, 1A at 250Vdc

Cord length

36 ft

Operating temperature - min

-29 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

221 °F

Connection

5-pin mini pigtail connector

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Cable type

SOOW-A

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50SA6PT](#)