

Eaton E50SAL6PC-R

Catalog Number: E50SAL6PC-R

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, 5 Pin Mini Connector, 10A at 240Vac, 1A at 125Vdc, 1NO-1NC, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K, LED (24–120Vac/dc), 10A, 1A, -40° to 250°F (-40° to 121°C), single pole

General specifications



Product Name

Eaton E50 NEMA heavy duty plug-in limit E50SAL6PC-R switch

Catalog Number

UPC

782113790442

Product Length/Depth

1.54 in

Product Height

3.58 in

Product Width

1.58 in

Product Weight

0.8688 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed

CSA Certified

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Contact Rating

10A at 240Vac, 1A at 125Vdc

Operating temperature - min

-40 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

250 °F

Connection

5-pin mini connector

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

LED indicator

LED (24-120 Vac/dc)

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50SAL6PC-R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)