

Eaton E50SAL6PC-W

Catalog Number: E50SAL6PC-W

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, 5 Pin Mini Connector, 10A at 240Vac, 1A at 125Vdc, 1NO-1NC, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K, with LED (24–120Vac/dc), 10A, 1A, -40° to 250°F (-40° to 121°C), single pole

General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50SAL6PC-W switch	UPC 782113055671
Product Length/Depth	Product Height
1.54 in	3.58 in
Product Width	Product Weight
1.58 in	0.8688 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

1 NO-1 NC

Contact Rating

10A at 240Vac, 1A at 125Vdc

Operating temperature - min

-40 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

250 °F

Connection

5-pin mini connector

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

LED indicator

LED (24-120 Vac/dc)

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50SAL6PC-W](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)