

Eaton E50SB6P24

Catalog Number: E50SB6P24

Eaton E50 Heavy Duty Factory Sealed 6P+ Limit Switch, 24 Ft. (7.3m) Cable, 10A at 240Vac, 1A at 250Vdc, SOOW-A, 2NO-2NC, 288Foot, Die Cast Zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K, 10A, 1A, -29° to 221°F (-34° to 105°C)



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50SB6P24
	UPC
	782113565279
Product Length/Depth	Product Height
1.54 in	3.58 in
Product Width	Product Weight
1.58 in	2.1188 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL Listed	
CSA Certified	

Product specifications

Enclosure material

Die cast zinc

Contact configuration

2 NO-2 NC

Contact Rating

10A at 240Vac, 1A at 250Vdc

Cord length

288 ft

Operating temperature - min

-29 °F

Maximum AC current

10 A

Maximum DC current

1 A

Operating temperature - max

221 °F

Connection

24 ft (7.3 m) cable

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67, IP69K

Cable type

SOOW-A

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50SB6P24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia