

# Eaton FWF3020VL

Catalog Number: FWF3020VL

Eaton Series C complete molded case circuit breaker, F-frame, FWF, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 20A, 690 Vac, 40 kAIC at 415 Vac, Line and load, 50°C

## General specifications



Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	FWF3020VL
	UPC
	786685388588

Product Length/Depth	Product Height
7.5 in	6 in

Product Width	Product Weight
5 in	5 lb

Certifications  
IEC Rated

## Product specifications

### Interrupt rating

40 kAIC at 415 Vac

### Frame

F

### Circuit breaker type

FWF

### Circuit breaker frame type

Complete breaker

### Terminals

Line and load

### Calibration

50°C

### Voltage rating

690 V AC

### Amperage Rating

20 A

### Trip Type

Fixed thermal, fixed magnetic

### Number of poles

Three-pole

## Resources

### Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

### Brochures

[Circuit breaker motor operators product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

### Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

### Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

### Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - FWF3020VL](#)