

Eaton HFW3020JVL

Catalog Number: HFW3020JVL

Eaton Series C complete molded case circuit breaker, F-Frame, HFW, Complete breaker, Adjustable thermal, adjustable magnetic trip type, Three-pole, 20A, 690 Vac, 70 kAIC at 415 Vac, Line and load, 50°C

General specifications



Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFW3020JVL
	UPC
	786685397474

Product Length/Depth	Product Height
3.38 in	6 in

Product Width	Product Weight
4.13 in	5 lb

Certifications
UL Listed

Product specifications

Interrupt rating

70 kAIC at 415 Vac

Frame

F

Circuit breaker type

HFW

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Calibration

50°C

Voltage rating

690 V AC

Amperage Rating

20 A

Trip Type

Adjustable thermal, adjustable magnetic

Number of poles

Three-pole

Resources

Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - HFW3020JVL](#)

[Series C F-Frame molded case circuit breakers](#)