

Eaton HFWF3063VL

Catalog Number: HFWF3063VL

Eaton Series C complete molded case circuit breaker, F-Frame, HFWF, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 63A, 240 Vac, 70 kAIC at 240 Vac, Line and load, 50°C



General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	HFWF3063VL
	UPC
	786685389189
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
4.13 in	5 lb
Certifications	
IEC Rated	

Product specifications

Interrupt rating

70 kAIC at 240 Vac

Frame

F

Circuit breaker type

HFWF

Circuit breaker frame type

Complete breaker

Terminals

Line and load

Calibration

50°C

Voltage rating

240 V AC

Amperage Rating

63 A

Trip Type

Fixed thermal, fixed magnetic

Number of poles

Three-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - HFWF3063VL](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Series C J-Frame molded case circuit breakers time current curves](#)